

MONOFOKAL

PANORAMA 2.0



Grupul de utilizatori vizat

Lentila monofocală Panorama 2.0 pentru confort și precizie mai mare, dar și pentru o claritate mai bună în comparație cu lentilele realizate prin metoda tradițională de producție.

Tehnologie

IOT Endless Single Vision

Metoda de producție

Prelucrarea suprafeței monofocale pe partea interioară a lentilei.

Comandarea dioptriilor

1/4, 1/8, 1/100

Parametri individuali


IPD, Vertex, Panto, Ztilt

Optimizare

Estetizare specială pentru lentilele care au dioptrii cu plus, pe baza formei ramei și a parametrilor de montare a lentilelor în ramă. În cazul în care comanda este plasată fără opțiunea de optimizare, topografia lentilei va fi decentrată nazal în raport cu centrul geometric cu 2.5 mm.

Marcaje pe lentile

- gravuri
- marcaje



MATERIALE

1.50 CR-39	1
1.53 Trivex	2
1.56 Mid. index	3
1.59 Poly	4
1.60 High Index	5
1.60 Tribrid	6
1.67 High Index	7
1.74 High Index	8

OPȚIUNI

Nici o opțiune	W	Transitions GEN 8 Sapphire	F	Nupolar Gray	S
Remove 400	H	Transitions GEN 8 Amethyst	M	Nupolar Gray Light	L
Remove 420	R	Transitions GEN 8 Amber	A	Nupolar Green	E
Remove 420 Photomatic Brown	O	Transitions GEN 8 Emerald	E	Transitions XTRActive Polarised Gray	X
Remove 420 Photomatic Gray	U	Transitions XTRActive Brown	C	Photomatic Brown	B
Transitions GEN 8 Brown	Z	Transitions XTRActive Gray	L	Photomatic Gray	I
Transitions GEN 8 Gray	N	Transitions XTRActive Green	K	DriveWear	D
Transitions GEN 8 Green	V	Nupolar Brown	B		